

64291 XIR

Low-voltage halogen lamps without reflector



Areas of application

- Lamps for special luminaires
- Medical fiber optics (HLX)

Product benefits

- Compared to standard lamps up to 10 % higher luminous efficacy (HLX)
- Instant light (HLX)

Product features

- Xenon instead of krypton as the filler gas (XENOPHOT HLX versions)
- Luminous flux up to 10 % higher with same power consumption (XENOPHOT HLX versions)
- HLX tungsten halogen low-voltage lamp with or without reflector
- Dimmable (HLX)



Product datasheet

Technical data


Electrical data

Nominal voltage	22.8 V
Nominal wattage	40.00 W

Photometrical data

Color temperature	3150 K
Nominal luminous flux	1200 lm

Dimensions & weight



Diameter	12.0 mm
Length	44.0 mm
Light center length (LCL)	30.0 mm ¹⁾
Filament length	3.90 mm
Illuminated field	3.9*1.4 mm ²
Filament diameter	1.4 mm

¹⁾ ±0.5 mm

Lifespan

Lifespan	800 h
----------	-------

Additional product data

Base (standard designation)	G6.35
Minimum diameter of lamp enclosure	12 mm

Capabilities

Dimmable	Yes
Burning position	h90

Product datasheet

Certificates & standards

EEI – Energy Label	B
--------------------	---


Country specific categorizations

Order reference	64291
-----------------	-------

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4008321330550	OSRH64291XIR	-	-	-
4008321330550	OSRH64291XIR	-	-	-

Product datasheet



Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321330550	64291 XIR	Folding carton box 1	25 mm x 23 mm x 70 mm	0.04 dm ³	4.00 g
4008321330567	64291 XIR	Shipping carton box 40	144 mm x 107 mm x 121 mm	1.86 dm ³	201.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.