Product datasheet



XBO R 100 W/45 OFR

XBO R \leq 450W with Reflector | Intense point source with precision pre-aligned reflector that provides a broad, continuous spectrum and has near perfect color rendering in the visible range



Areas of application

- Endoscopy
- Microscopy
- Surgical Headlamps
- Fiber Illumination
- Solar Simulation
- Imaging & Scanning

Product features and benefits

- High luminance / radiance with intense point source
- Broad, continuous spectral distribution
- High color rendering > 95
- High arc stability
- DC operation
- Hot restart capability
- Dimmable over a wide range
- Long lamp life



February 13, 2025, 03:03:49 XBO R 100 W/45 OFR

Technical data

General Product Information

Product number (Americas)	69197	
Product name (Americas)	XBO R 100W/45 OFR 2/CS 1/SKU	
Family brand XBO		
Lamp type	W/REFLECTOR	
Product remark	OFR = Ozone-free version	
Global order reference	XBO R 100 W/45 OFR	

Electrical Data


Nominal wattage	100 W
Lamp voltage	1214 V ¹⁾
Nominal current	7.2 A
Lamp current	7.07.4 A
Type of current	DC

Initial voltage range

Photometric Data

Nominal luminous flux	530 lm
Color temperature	6000 К
Color rendering index Ra	98
Focal length	45.0 mm

Physical Attributes & Dimensions



Lamp base	SPEZIAL
Diameter (in)	2.520 in
Diameter	64.0 mm
Length	93.0 mm

Product datasheet

Average life - horizontal

Product weight	110.00 g		
Operating Conditions			
Burning position	p20		
Cooling	Forced		
Lifetime Data			
Nominal lifetime	500 hr		

500 hr

Environmental & Regulatory Information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACh)

Primary article identifier	4050300317205	
Declaration no. in SCIP database	0ff25872-96e7-47f8-91ee-ef959f627d3e	
Candidate list substance 1	Lead	
CAS No. of substance 1	7439-92-1	
Safe use instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.	

Country specific information

Product code	METEL code	SEG-No.	STK-Number	UK Org
4050300317205	OSRXBOR100450FR	-	-	-

Product datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure in both the hot and cold state, XBO lamps must only be operated in appropriate enclosed casings. Always use the protective jackets supplied when handling these lamps. They may only be used as open lamps if appropriate safety measures are taken. More information is available on request or can be found in the leaflet included with the lamp or the operating instructions.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300317205	XBO R 100 W/45 OFR	Folding carton box 1	87 mm x 87 mm x 103 mm	0.79 dm³	148.00 g
4050300324777	XBO R 100 W/45 OFR	Shipping carton box 2	186 mm x 96 mm x 115 mm	2.05 dm³	342.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.